

# Tork Advanced Matic® Hand Towel Roll, 2-Ply

290092A



### Description

Soft, strong, and highly absorbent this towel offers the perfect combination of quality, performance, and value. Designed specifically for the Tork Elevation® Matic® Hand Towel Roll Dispensers, this Tork Advanced Matic Roll Towel offers a truly best-in-class product for no-touch, hygienic dispensing systems. Ideal for Class-A office buildings and upscale dining facilities.

- Long-lasting rolls minimize maintenance costs while maximizing service.
- One-at-a-time dispensing for reduced consumption and increased hygiene
- Environmental Label
- Advanced
- Tork Easy Handling ® Packaging
- 100 % Recycled

### Product Certifications



### Product Details

Print	No
Core inside diameter	1.49 in
Roll diameter	7.25 in
Embossing	Yes
Roll length	525 null
Roll width	7.75 in
Ply	2
System	H1
Color	White, White

### Shipping Data

	Consumer Units (CON)	Transport unit (TRP)	Pallet (PAL)
EAN	73286623461	10073286623468	7322540846157
Packaging Material	Roll	Carton	-
Pieces	1	6 (6 CON)	330 (55 TRP)
Height	7.28 in	9.13 in	100.38 in
Length	7.8 in	22.38 in	45 in
Width	7.28 in	15 in	37.38 in
Gross Weight		23.56 lb	1,296.09 lb
Net Weight	3.73 lb	22.38 lb	1,230.8 lb
Volume	0.24 ft	1.77 ft	97.7 ft
Layers Per Pallet	-	-	11
TRP Per Layer	-	-	5

# Tork Advanced Matic® Hand Towel Roll, 2-Ply

290092A

Compatible Products



DISP H1 ELEV Matic HWRT WHITE 1/CS  
5510202



DISP H1 ELEV Matic HWRT BLACK 1/CS  
5510282



Tork Matic HTR Disp -Intuition sensor Wh  
551100

Environmental Information

Content	<p>The product is made from</p> <p>Recycled fibers Chemicals</p> <p>The packaging material is made from paper or plastic.</p>
Material	<p>Recycled fibers</p> <p>Recycling of paper is an efficient use of resources as the wood fibers are used more than once.</p> <p>High demands are put on quality and purity of recovered fibers, considering each step of the chain (collecting, sorting, transporting, storage, use), to ensure safe and hygienic products.</p> <p>Recovered paper can be produced both from collected newsprint, magazines and office waste. The choice of recovered paper grades, is made for each product, depending on its specific requirements on performance properties and brightness. The paper is dissolved in water, washed and treated with chemicals under high temperature and screened to separate out impurities.</p> <p>Bleaching is a cleaning process of the fibers that is often used. The aim is then to achieve a bright pulp, but also to get a certain purity of the fiber in order to achieve the demands for hygiene products and in some cases to meet the requirements for food safety.</p> <p>Bleaching of the recovered pulp is made with chlorine-free bleaching agents (hydrogene peroxide and sodium dithionite). Except for Natural Napkins that are unbleached.</p> <p>For bleached products we use bleaching agents (to increase the brightness of pulp from recovered paper).</p>
Chemicals	<p>All chemicals (process aids as well as additives) are assessed from an environmental, occupational health and safety and product safety point of view.</p> <p>To control product performance we use additives:</p> <ul style="list-style-type: none"><li>• Wet strength agents (for Wipers and Hand Towels)</li><li>• Dry strength agents (is used together with mechanical treatment of the pulp to make strong products like wipers)</li><li>• For colored papers dyes and fixatives (to secure perfect fastness of the color) are added</li><li>• For printed products printing inks (pigments with carriers and fixatives) are applied</li><li>• For multi ply products we often use water soluble glue to secure the integrity of the product</li></ul>

# Tork Advanced Matic® Hand Towel Roll, 2-Ply

290092A

In most of our mills we do not add optical brighteners but it often occurs in recovered paper since it is used in printing paper.

We do not use softeners for professional hygiene products.

High product quality is secured through quality and hygiene management systems throughout production, storage and transport.

In order to maintain a stable process and product quality the paper manufacturing process is supported by the following chemicals/ process aids:

- defoamers (surfactants and dispersing agents)
- pH-control (sodium hydroxide and sulphuric acid)
- retention aids (chemicals that help to agglomerate small fibers to prevent fiber loss)
- Coating chemicals (that help to control the creping of the paper to make it soft and absorbent)

To reuse broke and to utilize recovered fibers we use:

- Pulping aid (chemicals that help to repulp wet strong paper)
- Flocculation chemicals (that help to clean out printing inks and fillers from recovered paper)
- Bleaching agents (to increase the brightness of pulp from recovered paper)

In the cleaning of our waste water we use flocculation agents and nutrients for the biological treatment to secure that no negative impact on water quality comes from our mills.

Environmental certification	This product is certified for FSC®.
Packaging	Fulfilment of Packaging and Packaging Waste Directive (94/62/EC): Yes
Article creation date and latest article revision	Date of issue: 19-04-2019 Revision date: 12-05-2025
Production	This product is produced at Essity Professional Hygiene NA Blending - US mill.
Destruction	This product is mainly used for personal hygiene and can be collected together with household waste.

Essity North America Inc., Cira Centre, Suite 2600 2929 Arch Street, Philadelphia, PA 19104, USA